

ReachUp™
Two-piece Toilet
K-26059K-0

3/4.5 L



Description

Reach Up 2PC Back-to-wall toilet with apron skirted bowl design and compact bowl length – 610mm to meet small bathroom needs. Rimless flushing technology that offers 360 degrees water flow rinsing the bowl thoroughly. Nowhere to hide for germs and dirt, ensuring thorough cleaning of the bowl.

| | |
|-------------------------|-----------------------------------|
| Model | K-26059K-0 |
| Dimension | W 406, D 610, H 770mm |
| Rough in | S TRAP, 225mm P TRAP, 185mm |
| Liters per flush | 3/4.5 L |
| Material used | Vitreous China |
| Available colors | White (0) |
| Test standard | |
| Included | Floor Mounting kit, P/N K-1072240 |

Required parts

Quiet Close Slim Seat K-24811K-0 | Rimless Bowl K-26056K-0 | Toilet Tank K-26060K-0
Connectors P-trap (1138552) or S-trap (1066987)
(Toilet bowl, tank and seat to be ordered as separate sku)

Technical drawing

