

Features

- Brass construction
- Leak-free ceramic disc valve with lifetime warranty
- Durable KOHLER finishes resist corrosion and tarnishing
- Flexible G1/2" supply hoses for easy installation
- Directionally adjustable, laminar-flow aerator
- Spout reach 151 mm
- Side control lever handle
- Includes pop-up drain
- Side control lever handle

SINGLE CONTROL LAVATORY FAUCET

K-73167T

ALSO K-73168T AND K-73170T



Codes/Standards Applicable

- GB 18145-2014
- EN 817-2008
- EN 200-2008


Installation Notes

Install this product according to the installation guide.

Specified Model

Model	Description	Color/Finished		
K-73167T-4	Composed Single Control Lavatory Faucet	<input type="checkbox"/> Polished Chrome (CP)	<input type="checkbox"/> French Gold (AF)	<input type="checkbox"/> Titanium (TT)
K-73168T-4	Composed Single Control Tall Lavatory Faucet	<input type="checkbox"/> Polished Chrome (CP)	<input type="checkbox"/> French Gold (AF)	<input type="checkbox"/> Titanium (TT)
K-73170T-4	Composed Single Control Super Tall Lavatory Faucet	<input type="checkbox"/> Polished Chrome (CP)	<input type="checkbox"/> French Gold (AF)	<input type="checkbox"/> Titanium (TT)

For a full range of color finishes in your market please contact your local Kohler representative.




Flow Curve

Note: Flow rates are approximate. (1 gallon = 3.785 liters, 1 bar = 14.5 psi)


Dimensions are approximate.

Unit: mm




K-73167T-4

Product Diagram



K-73168T-4



K-73170T-4

Product Diagram