



22544IN-**
BATH SPOUT
WITH DIVERTER




22543IN-**
BATH SPOUT
W/O DIVERTER

ROUGH-IN DIMENSIONS (in mm)

22543IN-**



22544IN-**




PRESSURE & HOT INLET TEMPERATURE



P (Bar) 0.5 < 3 < 5.5



3




T (°C) < 65




65

TOOLS REQUIRED




INSTALLATION INSTRUCTIONS


1




2




3



5












AERATOR CLEANING AND SERVICING




Ensure there is no leakage from the sides of aerator after tightening.

CLEANING INSTRUCTIONS

		 KOHLER CLEANING SOLUTION		
				

SERVICE PARTS



**.-Finish code must be specified when ordering.

THE BOLD LOOK
OF **KOHLER**®

Kohler India Corporation Pvt. Ltd.

6th Floor, Office Tower, Ambience Island,
NH-8, Gurugram-122002, Haryana, INDIA.

Customer Care : 1800 103 2244 (Toll Free) &
+91-124-4319685 / 86

Email : indiacustomer care@kohler.co.in

Website: www.kohler.co.in

All information is based on the latest product information available at the time of publication. Kohler Co. reserves the right to make changes in product characteristics, packaging or availability at any time without notice.