

Shift +

Round Multifunction Handshower

K-21335-G-CP



Description

Enjoy luxurious showering combined with up to 30 percent water savings. Hand shower provides three distinct sprays – full coverage, pulsating massage, or silk spray – all enhanced with Katalyst technology for a completely indulgent showering experience.

Model	K-21335-G-CP
Finish	Polished Chrome (CP)
Installation type	Bracket or slide bar required for wall-mount installation. Deck-mount holder required for deck-mount installation
Dimensions	W 29, H 251 mm
Flow Rate	6.6 LPM at 4.1 Bars
Features	<ul style="list-style-type: none"> - Advanced spray engine with 2 spray experiences: full-coverage and targeted massage. - Full-coverage spray produces an encompassing spray for everyday use and utilizes Katalyst® air induction to create large, full drops. - Targeted massage spray is a focused stream for targeting sore muscles or use as a utility spray. - Intuitive and easy push-button activation to switch between two sprays. - Ergonomic design is comfortable and easy to grip. - MasterClean™ sprayface resists hard water buildup and is easy to clean. - Contains flow-regulating check valve for backflow prevention

Can be paired with

- Contemporary Supply Elbow 16381T
- Flexible Shower Hose R12067T
- Rain-joy Slide bar 72740T

Technical drawing

