

Purist

Multifunction Handshower with Katalyst Air-Induction

K-22166-G-CP



Description

Enjoy luxurious showering combined with up to 30 percent water savings. This Purist hand shower provides three sprays - full coverage, pulsating massage, or silk spray - all enhanced with Katalyst technology for a completely indulgent showering experience

Model	K-22166-G-CP
Finish	Polished Chrome (CP), French Gold (AF), Brushed Nickel (BN), Brushed Bronze (BZ), Titanium (TT), Matte Black (BL)
Installation type	Bracket or slide bar required for wall-mount installation. Deck-mount holder required for deck-mount installation
Dimensions	W 127, H 284 mm
Flow Rate	6.6 LPM at 4.1 Bars
Features	<ul style="list-style-type: none"> - Advanced spray engine provides three experiences: full coverage, pulsating massage and silk spray. - Full-coverage spray produces an encompassing spray for everyday use and utilizes Katalyst® air induction to create large, full drops. - Pulsating massage spray targets sore muscles to ease away aches and pains. - Silk spray releases a dense, luxurious spray ideal for rinsing. - Thumb tab allows for a smooth transition between sprays.

Can be paired with

- Contemporary Supply Elbow 16381T
- Flexible Shower Hose R12067T
- Rain-joy Slide bar 72740T

Technical drawing

