

Traditional

Round Rainhead with Katalyst Air - 12"

K-13694-CP

Description

Enjoy a shower that simulates the soaking deluge of a warm summer downpour. This traditional-style rain head features innovative Katalyst air-induction technology, which efficiently mixes air and water to produce large water droplets and deliver a powerful, thoroughly drenching overhead shower experience.



Model	K-13694-CP
Finish	Polished Chrome (CP) French Gold (AF) Brushed Bronze (BV)
Installation type	1/2" - 14 NPT connection
Dimensions	W 316, H 316 mm
Flow rate	9.2 LPM at 4.1 Bars
Features	<ul style="list-style-type: none"> - Master Clean® spray nozzles to prohibit mineral build-up for easy cleaning. - Katalyst™ Spray Technology with air induction ball joint. - Optimized spray face for maximum performance. - Solid brass construction for durability and reliability.

Required

Shower arm and flange, one of the below options:

- 305 mm K-7392-CP/AF/BV/2BZ
- 152 mm K-7394-CP/AF/BV/2BZ
- 76 mm K-7396-CP

Technical drawing

