

Composed

Sensor Faucet, DC Mixer

K-20258T-B-CP



Description

Composed Deck Mount Sensor Faucets comes with contemporary elegant design to involve more styles for the commercial space.

Model	K-20258T-B-CP
Finish	Polished Chrome (CP)
Installation type	Deck Mount
Dimensions	Reach 148 mm, Height 123 mm
Flow rate	1.9 LPM at 4.1 Bars
Features	<ul style="list-style-type: none"> - Solid Metal Construction for Durability and Reliability - KOHLER ceramic disc valves exceed industry longevity standards by two times for a lifetime of durable performance - KOHLER finishes resist corrosion and tarnishing, exceeding industry durability standards over two times

Required

- DC Version: Power Supply (24484T-NA)

Technical drawing

