

## Oblo

Sensor Faucet, Cold Only

**K-9328T-CP (AC)**

**K-9329T-CP (DC)**

### Description

Composed Deck Mount Sensor Faucets comes with contemporary elegant design to involve more styles for the commercial space.



<b>Model</b>	<b>K-9328T-CP (AC)   K-9329T-CP (DC)</b>
<b>Finish</b>	Polished Chrome (CP)
<b>Installation type</b>	Deck Mount
<b>Dimensions</b>	Reach 127 mm, Height 234 mm
<b>Flow rate</b>	1.9 LPM at 4.1 Bars
<b>Features</b>	<ul style="list-style-type: none"> <li>- Solid Metal Construction for Durability and Reliability</li> <li>- KOHLER ceramic disc valves exceed industry longevity standards by two times for a lifetime of durable performance</li> <li>- KOHLER finishes resist corrosion and tarnishing, exceeding industry durability standards over two times</li> </ul>
<b>Included</b>	

### Required

- AC Version: Power Supply (16306T-NA)
- or Hybrid Energy System (13683T-NA)

### Technical drawing

