

## Loure

Wall-Mount Sensor Faucet, Cold Only with Drain

**K-98452T-B-CP (AC)**

**K-98453T-B-CP (DC)**



### Description

Loure Wall Mount Sensor Faucets comes with contemporary elegant design to involve more styles for the commercial space.

<b>Model</b>	<b>98452T-B-CP (AC)   K-98453T-B-CP (DC)</b>
<b>Finish</b>	Polished Chrome (CP)
<b>Installation type</b>	Wall Mount
<b>Dimensions</b>	Reach: 207 mm
<b>Flow rate</b>	1.9 LPM at 4.1 Bars
<b>Features</b>	<ul style="list-style-type: none"> <li>- Hidden sensor built in the spout to improve the experience</li> <li>- Waterfall spray makes the flow tender and avoid splash</li> <li>- Product tested for 24hour acid spray test to ensure long-lasting durability</li> </ul>

### Required

- AC Version: Power Supply (16306T-NA)
- or Hybrid Energy System (13683T-NA)
- DC Version: Power Supply (24484T-NA)

### Technical drawing

