

Loure

Sensor Faucet, Cold Only with Drain

K-98454T-B-CP (AC)

K-98455T-B-CP (DC)



Description

Loure Deck Mount Sensor Faucets comes with contemporary elegant design to involve more styles for the commercial space.

Model	K-98454T-B-CP (AC) K-98455T-B-CP (DC)
Finish	Polished Chrome (CP)
Installation type	Deck Mount
Dimensions	Reach: 101 mm, Height 136.5 mm
Flow rate	1.9 LPM at 4.1 Bars
Features	<ul style="list-style-type: none"> - Solid Metal Construction for Durability and Reliability - KOHLER ceramic disc valves exceed industry longevity standards by two times for a lifetime of durable performance - KOHLER finishes resist corrosion and tarnishing, exceeding industry durability standards over two times

Required

- AC Version: Power Supply (16306T-NA)
- or Hybrid Energy System (13683T-NA)
- DC Version: Power Supply (24484T-NA)

Technical drawing

