


99924AR-**



Kohler Africa (Pty) Ltd

Telephone: +27 (0) 11 050 9000
Email: contact.africa@kohler.com
www.africa.kohler.com


99924AR-** AQUA TURBO 360 MANUAL HIGH FLOW VALVE

BEFORE YOU BEGIN

All information is based on the latest product information available at the time of publication. Kohler Co. reserves the right to make changes in product characteristics, packaging, or availability at any time without notice.

Please leave these instructions for the consumer. They contain important information.

TOOLS REQUIRED



OPERATIONAL REQUIREMENTS



P 3 Bar (Recommended)
0.5 - 5.5 Bar (Operating range)
8 Bar (Maximum test pressure)




T < 65 (°C)

*Balanced supply is recommended.

ROUGH IN DIMENSIONS


99924AR-**




*All dimensions are in mm.

INSTALLATION INSTRUCTION


1




2



5



6



CLEANING INSTRUCTION

