

Beitou

Thermostatic High Flow Valve – 4 Outlet

K-77236IN-CP



Description

All new Automatic Thermostatic Kohler valve which automatically adjusts the water output to deliver your set temperature.

| | |
|--------------------------|--|
| Model | K-77236IN-CP |
| Finish | Polished Chrome (CP), Brushed Bronze (BV), BN-Brushed Nickel (BN), French Gold (AF) |
| Number of Outlets | 4 Maximum outlets working together 4 |
| Installation type | Wall Mount with concealed valve |
| Dimensions | W 164 mm H 437 mm |
| Features | <ul style="list-style-type: none"> - Thermostatic operation: automatically adjusts the water output to deliver set temperature - High performance: operates 4 outlets with 60 LPM max flow & 35 LPM flow from one outlet - Kohler engineered cartridge providing Protection against thermal shocks - Provides Anti-Scald protection - Safety Lock: Safety Button actuation for moving beyond set temperature - Flexibility to choose marking option matching with your choice of showering component |

Required

Thermostatic 4-way trim K-77247IN-9-CP/AF/BN/BV

Technical drawing

