

## Beitou

Thermostatic High Flow Valve – 6 Outlet

**K-77237IN-CP**



### Description

All new Automatic Thermostatic Kohler valve which automatically adjusts the water output to deliver your set temperature.

<b>Model</b>	<b>K-77237IN-CP</b>
<b>Finish</b>	Polished Chrome (CP), Brushed Bronze (BV), BN-Brushed Nickel (BN), French Gold (AF)
<b>Number of Outlets</b>	6   Maximum outlets working together 4
<b>Installation type</b>	Wall Mount with concealed valve
<b>Dimensions</b>	W 164, H 437 mm
<b>Features</b>	<ul style="list-style-type: none"> <li>- The calming movement of water lies at the heart of the Beitou™ collection.</li> <li>- Beitou high flow valves are Thermostatic valves for 4 or 6 outlets, which gives high Flow Rate of 60 L/min from 3 outlets.</li> <li>- Precise Temperature control due to toothed Ratchet mechanism.</li> <li>- Valves comes with cutting template and in-built spirit leveler is provided for easy alignment for Valves.</li> <li>- The valves are fitted with Kohler highly engineered thermostatic cartridge designed in UK to control preset temperature in case of Pressure or Temperature variation</li> </ul>

### Required

Thermostatic 4-way trim K-77247IN-9-CP/AF/BN/BV

### Technical drawing

