

Consonance®

6' Whirlpool Bath

K-1111-VLN-0

Features

- 6 hydromassage jets can be individually adjusted for water flow and direction.
- Variable-speed pump for adjusting hydromassage intensity.
- Two sets of 10 backjets target the lower back and shoulders to relieve tension and encourage deep breathing.
- 8 effervescence ports deliver gentle, caressing bubbles.
- Chromatherapy lighting allows you to select a preferred color scheme to suit your mood.
- Built-in heater.
- Remote control.
- Spacious design accommodates up to two bathers.
- Two distinct bathing wells and a cool-off area allow you to create your own experience.
- Two pillows provided for added comfort.



Codes/Standards

ASME A112.19.7/CSA B45.10

CSA B45.5/IAPMO Z124

ASTM E162

ASTM E662

UL 1795

CSA C22.2 No. 218.2

Model	K-1111-VLN-0
Material	Acrylic
Hydrotherapy	Effervescence
Available color	White
Installation	Drop-in

Required Products/Accessories

K-9696 Whirlpool 6-Jet Trim Kit

Recommended Products/Accessories

K-588 Under-Mount Installation Kit | K-1601 Bath/whirlpool footstop, removable | K-7167 2" adjustable pop-up drain

K-23726 Drain treatment | K-23732 Tub & shower cleaner

Required Electrical Service


Two dedicated circuits required, protected with Class A Ground-Fault Circuit-Interrupter (GFCI).

Outside North America, this device may be known as a Residual Current Device (RCD).

Pump, Heater: 220-240 V, 20 A, 50/60 Hz

Pump, Heater: 220-240 V, 20 A, 50/60 Hz

Technical Information	
Installation	Corner, Drop-in, Under-mount
Drain location	End
Basin area, bottom	45" x 43" (1143 mm x 1092 mm)
Basin area, top	57" x 57" (1448 mm x 1448 mm)
Weight	340 lbs (154.2 kg)
Minimum floor load	54 lbs/ft ² (263.7 kg/m ²)
Water depth	19-1/2" (495 mm)
Water capacity	170 gal (643.5 L)
Cutout	Drop-in, 68" x 68" (1727 mm x 1727 mm)
Electrical component rating	Pump: 220-240 V, 11 A, 50/60 Hz Heater: 220-240 V, 6.25 A, 50/60 Hz Pump: 220-240 V, 11 A, 50/60 Hz Heater: 220-240 V, 6.25 A, 50/60 Hz



Notes

Measure your actual product for rough-in details.
 Install this product according to the installation instructions.
 The hot water supply should be 70% of the capacity of the bath or greater. Installations will vary.
 Kit is required for under-mount installations (sold separately).
 If installing a rim-mount faucet, make sure there is no interference above or below the deck before drilling any holes.