


DROPLET FACEPLATE	K-4177IN-A-**
PEBBLE FACEPLATE	K-5413IN-**
D3 FACEPLATE	K-75891IN-**

BEVEL FACEPLATE	K-8857IN-A-**
LYNK FACEPLATE	K-75890IN-**
LYNK PNEUMATIC FACEPATE	K-75890IN-P-**

RECOMMENDED TOOLS*



INSTALLATION

1

For back inlet

a.

For top inlet

b.

For left inlet

c.

For right inlet

d.

*a. or b. or c. or d.

2

3

4

5

REMOTE INSTALLATION FOR PNEUMATIC ONLY

6

7

8.1

Connect Air Pipe For Pneumatic

























8.2

Install push Rods For Mechanical

9

OPERATION

SERVICE PARTS

1. 1278582-1 Fill Valve CJ101 (3L,6L) 	2. 1290889 Tank Outlet Pipe 	3. 1290891 Gasket Tank Outlet 	4. 1278774 Fill Valve Holder 	5. 1278882 Tablet Container 	6. 1292205 Push Bar (8") 
7. 1284859 Flush Valve Assembly 	8. 1278771 Air Actuation Assembly 	9. 1287206 Actuation Assembly Mechanical 	10. 1278609 Angle Valve Assembly 	11. 1278623 Flush Valve Lock Strip 	12. 1278575 Cap  (For product made before 01.12.2016)
13. 1282940 Flush Valve Seat Assembly 	14. 1278574 Square Mask Assembly 	15. Refer Table A BPP 	16. 1278572 Installation Hardware Kit 	17. 1278766-1 Screw, Self Tap M4, 25mm long 	18. 1278766-2 Screw, Self Tap M4, 75mm Long 
19. 1278615 Trap Assembly 	20. 1278581 Inlet Hose 	21. 1285260 Fill Valve Diaphragm 	22. 1285259 Flush Valve Diaphragm 	23. 1278580 Screen Filter 	24. 1278590 Seal, Rubber 
25. 1278588 Big O-Ring 	26. 1305948 Connector Assembly 	27. 1287600 Actuation Bracket Holder 	28. 1305950 Cap  (For product made after 01.12.2016)	29. 1285261 Flush Valve Link Assembly 	30. 1305053 Angle Valve Assembly 
31. 1283598 FLUSH AIR TUBES 		TABLE A			
		SKU CODE		PART NO.	
		8857IN-*/4177IN-*		1169511	
		5413IN-*		1222685	
		75890IN-*/75891IN-*		1243718	
		75890IN-P-*		1278604	
		5413IN-P-*		1297096	

WARRANTY

Kohler plumbing products are warranted to be free of defects in material and workmanship for 10 years in residential application and 5 years for non-residential application from the date of purchase.

Kohler India and its Authorized Service Franchise will make unit repairs or replacements under this warranty within a reasonable period of time, as determined by Kohler India or its Authorized Service Franchisee performing the repair or replacement.

Kohler is not responsible for labor charges, installation or other incidental or consequential costs. To obtain warranty service, contact Kohler India either through your Dealer, Plumbing Contractor or by calling number given below.

This warranty does not cover problems arising from poor/insufficient water quality beyond the recommended limits, excessive water impurities/hardness beyond the norms of drinking water, excessive humidity or improper care and cleaning.

This is Kohler Co.'s exclusive written warranty.

Contact us at: India Customer Service Center, Kohler India Corporation Pvt. Ltd., 6th Floor, Office Tower, Ambience Island, NH-8, Gurgaon, Haryana - 122001
(Customer Care:1800-103-2244, Monday-Saturday from 10:00AM to 06:00PM)