

Risk of personal injury or product damage. Handle with care.

Vitreous China can break or chip if the bolts and nuts are over-tightened, or if the product is handled carelessly.

- Observe all local plumbing and building codes.
- Carefully inspect the new lav for any damage. In case of any damage, please discard the product & contact Kohler customer care.
- User should preserve this document to order spare parts in future.

SPAN® ROUND WALL-MOUNT LAVATORY (SMALL).....	31458IN-0
SPAN® ROUND WM LAVATORY(SMALL) W HALF PED.....	24560IN-0
INCLUDES SPAN® ROUND WALL-MOUNT LAVATORY (SMALL).....	31458IN-0
INCLUDES FOLIO™ HALF-PEDESTAL.....	11340IN-0

SPAN® ROUND WM LAVATORY(SMALL) W FULL PED.....	24561IN-0
INCLUDES SPAN® ROUND WALL-MOUNT LAVATORY (SMALL).....	31458IN-0
INCLUDES FOLIO™/ PATIO® PEDESTAL.....	2019IN-0

SPAN® SQUARE WALL-MOUNT LAVATORY.....	25317IN-0
SPAN® SQUARE WM LAVATORY W HALF PED.....	24558IN-0
INCLUDES SPAN® SQUARE WALL-MOUNT LAVATORY.....	25317IN-0
INCLUDES FOLIO™ HALF-PEDESTAL.....	11340IN-0


SPAN® SQUARE WM LAVATORY W FULL PED.....	24559IN-0
INCLUDES SPAN® SQUARE WALL-MOUNT LAVATORY.....	25317IN-0
INCLUDES FOLIO™/ PATIO® PEDESTAL.....	2019IN-0

SPAN® SQUARE WALL-MOUNT LAVATORY (SMALL).....	31460IN-0
SPAN® SQUARE WM LAV(SMALL) W HALF PED.....	24563IN-0
INCLUDES SPAN® SQUARE WALL-MOUNT LAVATORY (SMALL).....	31460IN-0
INCLUDES FOLIO™ HALF-PEDESTAL.....	11340IN-0

SPAN® SQUARE WM LAV(SMALL) W FULL PED.....	24562IN-0
INCLUDES SPAN® SQUARE WALL-MOUNT LAVATORY (SMALL)...	31460IN-0
INCLUDES FOLIO™/PATIO® PEDESTAL.....	2019IN-0


31458IN-0

Wall Mount Lavatory Installation



25317IN-0


Wall Mount Lavatory Installation




31460IN-0

Unit: Inches (cm)


Wall Mount Lavatory Installation




Half-Pedestal Lavatory




Half-Pedestal Lavatory




Half-Pedestal Lavatory




Full-Pedestal Lavatory



Full-Pedestal Lavatory



Full-Pedestal Lavatory



NOTES:

- Fixture dimensions are nominal and confirm to tolerances as per ASME Standard A112.19.2M.
- Product illustrations shown are representative only; actual product may vary.
- Kohler reserves the right to make changes in product characteristics, packaging or availability at any time without notice.

CAUTION : Do not use white cement or high lime-cement to install this lav. The expansion of cement due to rise in temperature may cause the lav to crack or be damaged. Kohler is not responsible for any damage due to installation with the use of cement.

WALL-MOUNT LAVATORY INSTALLATION INSTRUCTIONS

1

NOTE: Refer Roughing-in for dimensions A & B

2

NOTE: Refer manufacturer's Installation Instruction for Installation of Faucet, Drain & Bottle Trap with lavatory.

3

8-10 N-m / 6-9 turns (1 turn = 45°)

4

HALF-PEDESTAL INSTALLATION INSTRUCTIONS

1

Bottom View of Lavatory

2

8-10 N-m / 6-9 turns (1 turn = 45°)

3

FULL-PEDESTAL INSTALLATION INSTRUCTIONS

1

Bottom View of Lavatory

2

8-10 N-m / 6-9 turns (1 turn = 45°)

3

8-10 N-m / 6-9 turns (1 turn = 45°)

4

8-10 N-m / 6-9 turns (1 turn = 45°)

5


8-10 N-m / 6-9 turns (1 turn = 45°)

6


Recommended Bottle Trap

Recommended Drain


Recommended Spare Parts



K-75823IN-**/
K-7314IN-**



K-45432IN-**



1223187
Mounting Kit

**Finish code must be specified when ordering.