

Oblo

Invisible Sensor Faucet

K-8397T-CP (DC)

K-8399T-CP (AC)



Description

AC touchless faucets with Insight technology features an adaptive infrared sensor that gathers and analyzes the surrounding area upon installation. After recording these details, Insight calibrates the sensor to filter false triggers and optimize the faucet's operation.

Model	K-8397T-CP (DC) K-8399T-CP (AC)
Finish	Polished Chrome (CP)
Installation type	Deck Mount
Dimensions	Reach: 132 mm, Height till aerator 290 mm
Flow rate	1.9 LPM at 4.1 Bars
Features	<ul style="list-style-type: none"> - Kinesis™ technology with concealed sensor allows for a clean aesthetic and provides extraordinarily accurate and reliable actuation in varying installation environments. Below-counter valving reduces the faucet footprint. - Design-forward aesthetic for commercial bathroom spaces. - AA battery-powered; up to four-year battery life (approx. 105,000 cycles). - On-demand usage with 30-second max. continual run cycle to prevent vandalism and save water. Vandal-resistant aerator. - Includes grid drain (K-7129-A).

Can be Paired With

- Connection kit to become a mixer K-1240574-SP
- Thermostatic valve to become a thermostatic mixer K-16294T-3-CP
- Hybrid energy system K-13683T-NA

Technical drawing

